#### **AD130**

### Professional Multi-Parameter Splash-Proof pH-ORP-Temp Portable Meter

AD130 is a heavy-duty portable pH meter designed to provide laboratory results and accuracy even under harsh industrial conditions.

- 7 memorized buffers for pH calibration (pH 1.68, 4.01, 6.86, 7.01, 9.18, 10.01 and 12.45)
- Messages on the LCD to make the calibration easy and accurate
- pH readings with manual or automatic
- Temperature compensation
- pH calibration using pH buffers with 0.01 resolution
- Temperature range from -20 to 120°C (-4 to  $248^{\circ}\text{F}$ ) using A7662 probe

AD130 can also use ORP electrodes to measure mV, with a resolution up to 0.1 mV.



#### AD130 is supplied with

AD1230B - pH electrode with epoxy body, double junction, BNC connector and 1 m cable; AD7662 - Stainless steel temperature probe with 1 m cable; AD70004 - pH4 calibration solution in sachet (20 ml), AD70007 - pH7 calibration solution in sachet (20 ml); Wrist strap; Batteries (4 x 1.5V, AA alkaline); Instruction manual

## Optional AD3230B - ORP

 Gel filled combination ORP electrode with platinum contact



#### Accessories

Find an accessory guide for portable meters on page 13

#### AD131 - AD132

## Professional Waterproof pH-ORP-Temperature Portable Meter with GLP & RS232 interface

AD131 and AD132 are heavy-duty portable waterproof meters for pH, ORP (Oxidation Reduction Potential) and temperature

measurements, designed to provide laboratory results and accuracy even under harsh industrial conditions.

- 7 memorized buffers for pH calibration (pH 1.68, 4.01, 6.86, 7.01, 9.18, 10.01 and 12.45)
- Messages on the LCD to make the calibration easy and accurate
- pH readings with manual or automatic temperature compensation
- Calibration time-out alarm
- · Log-on-demand
- HOLD feature to freeze stable reading on the LCD
- GLP feature to view last calibration data for pH and relative mV
- PC interface [AD132]
- AD132 allows connection to an external serial printer with the following specification: at least 16 characters/line, baud rate 9600 and 9-pin RS232 input



# AD131 and AD132 are supplied with

AD1230B - pH electrode with epoxy body, double junction, BNC connector and 1 m cable; AD7662 - Stainless steel temperature probe with 1 m cable; AD70004 - pH4 calibration solution in sachet (20 ml); AD70007 - pH7 calibration solution in sachet (20 ml); Wrist strap; Batteries (4 x 1.5V, AA alkaline); Instruction manual; AD9551 - Serial communication cable [AD132]

## Optional AD3230B - ORP electrode

 Gel filled combination ORP electrode with platinum contact



### Accessories

Find an accessory guide for portable meters on page 13

		AD130	AD131 - AD132
Range	рН	-2.00 to 16.00	-2.00 to 16.00
	ORP	±1999 mV	±2000 mV
	Temp	-20.0 to 120.0°C / -4.0 to 248.0°F	-20.0 to 120.0°C / - 4.0 to 248.0°F
Resolution	рН	0.01 pH	0.01 pH
	ORP	0.1 ±699.9 mV / 1 mV (outside)	0.1 mV (±999.9 mV) / 1 mV (outside)
	Temp	0.1°C (0.1°F)	0.1°C (0.1 °F)
Accuracy (at 25°C/77°F)	рН	± 0.01 pH	±0.01 pH
	ORP	±0.2 up to ±699.9 mV / ±1 mV (outside)	$\pm 0.2$ mV up to $\pm 699.9$ mV / $\pm 0.5$ mV up to $\pm 999.9$ mV / $\pm 2$ mV (outside)
	Temp	±0.4°C (±0.8°F) (excluding probe error)	±0.4°C (±0.7°F) (excluding probe error)
Calibration	рН	1 or 2 point calibration, 7 standard buffers available (pH 1.68, 4.01, 6.86, 7.01, 9.18, 10.01, 12.45)	Up to 5-point calibration, with 7 standard buffers (pH 1.68, 4.01, 6.86, 7.01 9.18, 10.01, 12.45)
	ORP	Factory calibrated	Factory calibrated
Temperature compensation		ATC/MTC, -20.0 to 120.0°C (-4.0 to 248.0°F)	ATC/MTC, -20 to 120°C (-4.0 to 248.0 °F)
Unit		°C and °F	°C and °F
Memory		-	Log-on-demand 500 samples
GLP		=	Yes (With time stamp)
Hold function		Yes	Yes (Auto End Point)
Low battery indication		Yes	-
Stability indicator		Yes	Yes
Auto shutt-off		20 min. (can be disabled)	5 min. (can be disabled)
PC Interface		-	RS232 for PC software and External Printer [AD132]
Probe (Included)		AD1230B - epoxy body pH electrode with double junction, BNC connector and 1	m cable; AD7662 - Stainless steel temperature probe with 1 m cable
Battery Type / Life		4 x 1.5V AA batteries / Approx. 500 hours of continuous use	4 x 1.5V AA batteries / Approx. 300 hours of continuous use
Dimensions / Weight		188 x 96 x 70 mm / 460 g	188 x 96 x 70 mm / 460 g